


Cascade PM8

200 mm Manual Probe System



Microscope movement

- 150 mm x 100 mm manual movement for large area evaluation
- 50 mm x 50 mm high-resolution movement for precise work with > 20x objectives
- 50 mm x 50 mm motorized movement for easy navigation and heavy-duty microscope integration
- 200 mm x 200 mm movable bridge with coarse and fine movement for large area inspection

Microscope bridge

- Cast bridge for maximum microscope stability and low drift
- Low-profile design for ergonomic microscope operation

Probe platen

- Compatible with probe card adapters
- Probe cards and positioners can be used simultaneously
- Large space to fit several positioners on each side
- mm-Wave platen for 110 GHz load pull and other RF noise applications
- Cooled platen for chucks up to 300 °C

Platen movement

- 45 mm travel range for maximum flexibility
- System height can adapt easily from wafer to package board application
- Motorized movement option for quick operation

Platen separation

- 500 µm separation drive with 1 µm precision repeatable movement to contact position

Chuck theta movement

- Fine theta movement $\pm 6^\circ$ for exact RF probe tip alignment

Chuck Z movement

- 8 mm load stroke for safe and easy wafer exchange

Chuck

- Dedicated 200 mm chucks for general purpose, RF, triaxial measurements and high temperatures up to 300 °C available
- Excellent planarity

Microscope and camera

- High-resolution microscopes (eVue™ FS70, PSM1000) for work on small features, even with laser cutter option
- Stereo microscopes for easy work with RF probe tips
- C-mount camera option for simple navigation and documentation

Positioner

- Compatible with all Cascade Microtech positioners down to submicron positioning capability
- Various probe arms for accurate I-V, C-V and RF measurements available
- Positioners interchangeable with other Cascade probe stations: MPS150, EFS150, PM300, PA200, PA300

Chuck XY-movement

- Rapid independent x-y stage coarse movement
- Precise movement allows chuck positioning with <1 µm resolution
- Separate axis fixation for easy navigation along lines
- Highly rigid stage design

Base platen

- Small footprint
- Easy operation of chuck and platen drives

Fine movement and stage indicator

- Easy view of actual x-y fine position

Vacuum switch

©Copyright 2022 FormFactor, Inc. All rights reserved. FormFactor and the FormFactor logo are trademarks of FormFactor, Inc. All other trademarks are the property of their respective owners. All information is subject to change without notice.